



# **MCM258**

### 800mm Cable Managed Leg Frame






# TOOLS REQUIRED FOR ASSEMBLY Sample of the same of the








ALWAYS HANDLE ITEMS WITH CARE





IF UNSURE CALL FOR ASSISTANCE






KEEP FITTINGS AWAY FROM CHILDREN





### Please check that you have all the components!






### Please check that you have all the hardware!






# Step 1 Place your desktop face down onto a clean dry surface and knock in the nylon inserts into the pre drilled holes on the underside of the desktop. Nylon M6x10 Socket RM-PAR05 X4


Step 2 Screw the 25mm adjustable feet into the bottom of both leg frames.










Step 3
Attach the LH leg to the desktop using the M6x50mm connect bolts.





Step 4 Attach the modesty panel to the leg using the 70mm confirmat screws.










6


### Step 5


Place the RH leg frame onto the desktop and attach to the modesty panel using the 70mm confirmat screws.




















### Step 9

Feed any cables up through the cable channel from the inside of the leg. If needed use the cable ties to fasten them to the cable channel.

### Step 10


10

Insert the cable cover into the opening between the uprights. Repeat this step for both legs.




### Step 11

Attach the cable covers using the M6x10mm thumbscrews. Repeat this step for both legs.








## **Desk Pedestals**


























### Please check that you have all the fittings





Minifix cam 15N CAM03




Quickfix spread bolt BLT06




1"1/4 x 8 screw SCR12

253F



Minifix cam 15N

### Handle screw M4x22



Quickfix spread bolt



1"1/4 x 8 screw SCR12

R2F





4 Minifix cam 15N CAM03




4 Quickfix spread bolt BLT06



4 1"1/4 x 8 screw SCR12





4 M4x22 COMBI BOLT SCR25



2 CH/LF (LARGO) HANDLE HDL09

R3F









4 Minifix cam 15N CAM03

4 Quickfix spread bolt BLT06

1"1/4 x 8 screw

6 M4x22 COMBI BOLT SCR25

3 CH/LF (LARGO) HANDLE HDL09



